

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203843

Luminaire Tested: **LSR6B15D010BZ EC6B10208040 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208040 6LBNGPH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 763.9 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203843

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203843

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																																				
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																																				
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																																				
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																																				
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70																																				
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																																				
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																																				
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58																																				
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																																				
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203843

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	11.0
10°-20°	207.3	27.1
20°-30°	251.2	32.9
30°-40°	171.2	22.4
40°-50°	40.8	5.3
50°-60°	6.4	0.8
60°-70°	2.3	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.6	71.0
0°-40°	713.7	93.4
0°-60°	760.9	99.6
0°-90°	763.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	929	
5°	902	84
15°	742	207
25°	549	251
35°	274	171
45°	44	41
55°	7	6
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203843

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	928.6
2.5°	923.3
5°	902.4
7.5°	874.5
10°	834.5
12.5°	789.2
15°	742.1
17.5°	693.4
20°	644.6
22.5°	595.8
25°	548.8
27.5°	505.2
30°	442.5
32.5°	360.6
35°	273.5
37.5°	195.1
40°	128.9
42.5°	80.1
45°	43.6
47.5°	22.6
50°	12.2
52.5°	8.7
55°	7.0
57.5°	5.2
60°	3.5
62.5°	3.5
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)