

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205120

Luminaire Tested: **LSR6B40D010BZ EC6B30509027 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509027 6LBML1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3070.5 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205120

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205120

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205120

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.0	11.5
10°-20°	881.3	28.7
20°-30°	1024.5	33.4
30°-40°	627.4	20.4
40°-50°	155.8	5.1
50°-60°	18.2	0.6
60°-70°	6.8	0.2
70°-80°	2.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2259.7	73.6
0°-40°	2887.1	94.0
0°-60°	3061.1	99.7
0°-90°	3070.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3070.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3843	
5°	3792	354
15°	3163	881
25°	2267	1024
35°	982	627
45°	173	156
55°	16	18
65°	8	7
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P205120

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBML11

CANDELA DISTRIBUTION (FULL):

0°	
0°	3842.6
2.5°	3838.6
5°	3791.5
7.5°	3689.3
10°	3551.8
12.5°	3371.1
15°	3162.8
17.5°	2938.9
20°	2718.9
22.5°	2498.8
25°	2267.0
27.5°	1999.9
30°	1693.4
32.5°	1335.9
35°	982.2
37.5°	691.5
40°	471.5
42.5°	294.7
45°	172.9
47.5°	98.2
50°	51.1
52.5°	23.6
55°	15.7
57.5°	11.8
60°	11.8
62.5°	7.9
65°	7.9
67.5°	3.9
70°	3.9
72.5°	3.9
75°	3.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)