

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203370

Luminaire Tested: **LSR6B40D010BZ EC6B30509027 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509027 6LBMWH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2708.8 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203370

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203370

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66																			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58																			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55																			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203370

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.9	11.4
10°-20°	758.4	28.0
20°-30°	877.5	32.4
30°-40°	560.9	20.7
40°-50°	159.0	5.9
50°-60°	28.4	1.0
60°-70°	11.6	0.4
70°-80°	4.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1944.9	71.8
0°-40°	2505.8	92.5
0°-60°	2693.2	99.4
0°-90°	2708.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2708.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3379	
5°	3319	309
15°	2720	758
25°	1936	878
35°	885	561
45°	185	159
55°	26	28
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P203370

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3379.2
2.5°	3375.5
5°	3318.9
7.5°	3217.2
10°	3074.1
12.5°	2908.3
15°	2720.0
17.5°	2524.1
20°	2331.9
22.5°	2143.6
25°	1936.4
27.5°	1710.3
30°	1457.9
32.5°	1175.4
35°	885.3
37.5°	640.4
40°	444.5
42.5°	293.8
45°	184.6
47.5°	109.3
50°	64.0
52.5°	37.7
55°	26.4
57.5°	22.6
60°	18.8
62.5°	15.1
65°	11.3
67.5°	7.5
70°	7.5
72.5°	3.8
75°	3.8
77.5°	3.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)