

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204669

Luminaire Tested: **LSR6B15D010BZ EC6B10208040 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208040 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1704.6 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204669

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204669

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204669

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	3.8
10°-20°	185.5	10.9
20°-30°	279.3	16.4
30°-40°	332.4	19.5
40°-50°	331.8	19.5
50°-60°	269.8	15.8
60°-70°	166.0	9.7
70°-80°	64.3	3.8
80°-90°	10.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.9	31.1
0°-40°	862.3	50.6
0°-60°	1464.0	85.9
0°-90°	1704.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1704.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	685	65
15°	658	185
25°	608	279
35°	532	332
45°	431	332
55°	302	270
65°	167	166
75°	59	64
85°	8	10
90°	0	



TEST NUMBER: P204669

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	686.8
2.5°	687.8
5°	684.8
7.5°	680.7
10°	675.7
12.5°	666.6
15°	658.5
17.5°	646.4
20°	633.3
22.5°	621.1
25°	608.0
27.5°	589.8
30°	571.6
32.5°	554.5
35°	532.3
37.5°	508.0
40°	485.8
42.5°	458.5
45°	431.3
47.5°	402.0
50°	370.7
52.5°	338.3
55°	302.0
57.5°	266.6
60°	232.3
62.5°	199.0
65°	166.6
67.5°	136.3
70°	108.1
72.5°	81.8
75°	58.6
77.5°	38.4
80°	23.2
82.5°	14.1
85°	8.1
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)