

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202850

Luminaire Tested: **LSR6B40D010BZ EC6B30508030 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30508030 6LBWWH1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3819.5 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202850

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202850

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 92  |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 75  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 71  | 79  | 74  | 71  | 77  | 73  | 70  | 68  |
| 5   | 87  | 77  | 71  | 66  | 85  | 76  | 70  | 65  | 75  | 69  | 65  | 73  | 68  | 64  | 71  | 67  | 63  | 62  |
| 6   | 82  | 71  | 64  | 59  | 80  | 71  | 64  | 59  | 69  | 63  | 59  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  | 63  | 57  | 53  | 61  | 57  | 53  | 51  |
| 8   | 72  | 61  | 54  | 49  | 71  | 61  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 47  |
| 9   | 68  | 57  | 50  | 45  | 67  | 56  | 50  | 45  | 55  | 49  | 45  | 54  | 49  | 45  | 53  | 48  | 45  | 43  |
| 10  | 64  | 53  | 46  | 42  | 63  | 53  | 46  | 42  | 52  | 46  | 42  | 51  | 45  | 42  | 50  | 45  | 41  | 40  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202850

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWWH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 228.0  | 6.0       |
| 10°-20°   | 678.1  | 17.8      |
| 20°-30°   | 1020.7 | 26.7      |
| 30°-40°   | 1043.7 | 27.3      |
| 40°-50°   | 633.8  | 16.6      |
| 50°-60°   | 178.5  | 4.7       |
| 60°-70°   | 27.1   | 0.7       |
| 70°-80°   | 8.8    | 0.2       |
| 80°-90°   | 0.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1926.9 | 50.4      |
| 0°-40°    | 2970.5 | 77.8      |
| 0°-60°    | 3782.9 | 99.0      |
| 0°-90°    | 3819.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3819.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2372 |      |
| 5°  | 2382 | 228  |
| 15° | 2401 | 678  |
| 25° | 2228 | 1021 |
| 35° | 1692 | 1044 |
| 45° | 815  | 634  |
| 55° | 177  | 178  |
| 65° | 24   | 27   |
| 75° | 10   | 9    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P202850

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2372.3 |
| 2.5°  | 2372.3 |
| 5°    | 2381.9 |
| 7.5°  | 2396.3 |
| 10°   | 2396.3 |
| 12.5° | 2405.9 |
| 15°   | 2401.1 |
| 17.5° | 2391.5 |
| 20°   | 2357.9 |
| 22.5° | 2310.0 |
| 25°   | 2228.5 |
| 27.5° | 2137.5 |
| 30°   | 2012.9 |
| 32.5° | 1864.3 |
| 35°   | 1691.8 |
| 37.5° | 1500.1 |
| 40°   | 1279.6 |
| 42.5° | 1049.6 |
| 45°   | 814.7  |
| 47.5° | 603.9  |
| 50°   | 426.5  |
| 52.5° | 287.6  |
| 55°   | 177.3  |
| 57.5° | 105.4  |
| 60°   | 52.7   |
| 62.5° | 33.5   |
| 65°   | 24.0   |
| 67.5° | 19.2   |
| 70°   | 14.4   |
| 72.5° | 9.6    |
| 75°   | 9.6    |
| 77.5° | 4.8    |
| 80°   | 4.8    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)