

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203371

Luminaire Tested: **LSR6B40D010BZ EC6B30509030 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509030 6LBMWH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2816.4 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203371

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203371

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203371

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.2	11.4
10°-20°	788.5	28.0
20°-30°	912.4	32.4
30°-40°	583.2	20.7
40°-50°	165.3	5.9
50°-60°	29.5	1.0
60°-70°	12.1	0.4
70°-80°	4.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2022.1	71.8
0°-40°	2605.3	92.5
0°-60°	2800.2	99.4
0°-90°	2816.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2816.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3514	
5°	3451	321
15°	2828	789
25°	2013	912
35°	920	583
45°	192	165
55°	27	30
65°	12	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P203371

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3513.5
2.5°	3509.6
5°	3450.8
7.5°	3345.1
10°	3196.2
12.5°	3023.9
15°	2828.0
17.5°	2624.3
20°	2424.6
22.5°	2228.7
25°	2013.3
27.5°	1778.3
30°	1515.9
32.5°	1222.1
35°	920.5
37.5°	665.9
40°	462.2
42.5°	305.5
45°	191.9
47.5°	113.6
50°	66.6
52.5°	39.2
55°	27.4
57.5°	23.5
60°	19.6
62.5°	15.7
65°	11.8
67.5°	7.8
70°	7.8
72.5°	3.9
75°	3.9
77.5°	3.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)