

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203123

Luminaire Tested: **LSR6B15D010BZ EC6B10208050 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208050 6LBWMW1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1434.8 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203123

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203123

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77																			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68																			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60																			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37																			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203123

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.9	5.3
10°-20°	212.8	14.8
20°-30°	306.6	21.4
30°-40°	318.3	22.2
40°-50°	235.4	16.4
50°-60°	140.6	9.8
60°-70°	85.4	6.0
70°-80°	46.8	3.3
80°-90°	13.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.3	41.5
0°-40°	913.6	63.7
0°-60°	1289.6	89.9
0°-90°	1434.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1434.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	806	
5°	800	76
15°	755	213
25°	668	307
35°	513	318
45°	303	235
55°	153	141
65°	85	85
75°	44	47
85°	10	13
90°	0	



TEST NUMBER: P203123

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	805.8
2.5°	805.8
5°	800.5
7.5°	793.6
10°	783.1
12.5°	770.9
15°	755.3
17.5°	737.9
20°	720.5
22.5°	696.1
25°	668.3
27.5°	638.7
30°	600.4
32.5°	562.1
35°	513.4
37.5°	462.9
40°	407.2
42.5°	353.3
45°	302.8
47.5°	257.6
50°	217.5
52.5°	182.7
55°	153.1
57.5°	130.5
60°	111.4
62.5°	97.5
65°	85.3
67.5°	74.8
70°	64.4
72.5°	53.9
75°	43.5
77.5°	34.8
80°	26.1
82.5°	19.1
85°	10.4
87.5°	5.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)