

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202753

Luminaire Tested: **LSR6B40D010BZ EC6B30509030 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509030 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3155.7 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202753

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202753

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202753

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	5.8
10°-20°	521.6	16.5
20°-30°	764.8	24.2
30°-40°	796.0	25.2
40°-50°	550.7	17.5
50°-60°	239.8	7.6
60°-70°	73.5	2.3
70°-80°	22.0	0.7
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1470.3	46.6
0°-40°	2266.2	71.8
0°-60°	3056.7	96.9
0°-90°	3155.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3155.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1946	
5°	1938	184
15°	1852	522
25°	1672	765
35°	1288	796
45°	712	551
55°	258	240
65°	70	74
75°	20	22
85°	4	3
90°	0	



TEST NUMBER: P202753

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1946.4
2.5°	1950.5
5°	1938.2
7.5°	1921.8
10°	1901.4
12.5°	1881.0
15°	1852.3
17.5°	1815.5
20°	1774.6
22.5°	1729.7
25°	1672.4
27.5°	1598.8
30°	1504.8
32.5°	1406.6
35°	1288.0
37.5°	1157.2
40°	1005.9
42.5°	854.6
45°	711.5
47.5°	576.6
50°	458.0
52.5°	347.6
55°	257.6
57.5°	184.0
60°	126.8
62.5°	94.0
65°	69.5
67.5°	53.2
70°	36.8
72.5°	28.6
75°	20.4
77.5°	12.3
80°	8.2
82.5°	4.1
85°	4.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)