

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204787

Luminaire Tested: **LSR6B20D010BZ EC6B10209024 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209024 6LBCSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1617.2 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204787

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204787

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87	87	87	87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74	74	74	74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63	63	63	63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55	55	55	55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48	48	48	48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42	42	42	42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37	37	37	37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33	33	33	33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30	30	30	30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27	27	27	27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204787

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	3.9
10°-20°	178.2	11.0
20°-30°	268.0	16.6
30°-40°	317.6	19.6
40°-50°	316.1	19.5
50°-60°	254.8	15.8
60°-70°	154.1	9.5
70°-80°	57.2	3.5
80°-90°	8.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.8	31.5
0°-40°	826.4	51.1
0°-60°	1397.4	86.4
0°-90°	1617.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1617.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	658	63
15°	631	178
25°	582	268
35°	509	318
45°	412	316
55°	284	255
65°	155	154
75°	52	57
85°	7	9
90°	0	



TEST NUMBER: P204787

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	660.5
2.5°	660.5
5°	657.6
7.5°	655.6
10°	649.8
12.5°	640.0
15°	631.1
17.5°	621.3
20°	609.6
22.5°	597.8
25°	582.1
27.5°	565.5
30°	546.9
32.5°	529.2
35°	508.6
37.5°	487.1
40°	461.6
42.5°	437.1
45°	411.6
47.5°	383.2
50°	351.8
52.5°	319.5
55°	284.2
57.5°	252.9
60°	217.6
62.5°	186.2
65°	154.8
67.5°	125.4
70°	98.0
72.5°	73.5
75°	51.9
77.5°	33.3
80°	19.6
82.5°	11.8
85°	6.9
87.5°	2.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)