

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203788

Luminaire Tested: **LSR6B40D010BZ EC6B30509730 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509730 6LBNWH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2100.9 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203788

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203788

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66																			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63																			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60																			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203788

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.2	16.6
10°-20°	670.9	31.9
20°-30°	609.9	29.0
30°-40°	369.7	17.6
40°-50°	84.2	4.0
50°-60°	10.7	0.5
60°-70°	4.8	0.2
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1630.0	77.6
0°-40°	1999.8	95.2
0°-60°	2094.7	99.7
0°-90°	2100.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2100.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4125	
5°	3889	349
15°	2416	671
25°	1322	610
35°	586	370
45°	93	84
55°	11	11
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203788

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBNWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4124.8
2.5°	4074.7
5°	3888.9
7.5°	3588.6
10°	3206.2
12.5°	2809.4
15°	2416.2
17.5°	2058.8
20°	1758.6
22.5°	1515.5
25°	1322.5
27.5°	1150.9
30°	982.9
32.5°	786.4
35°	586.2
37.5°	411.0
40°	271.6
42.5°	168.0
45°	92.9
47.5°	42.9
50°	17.9
52.5°	14.3
55°	10.7
57.5°	10.7
60°	7.1
62.5°	7.1
65°	3.6
67.5°	3.6
70°	3.6
72.5°	3.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)