

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203240

Luminaire Tested: **LSR6B20D010BZ EC6B10209024 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209024 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1076.2 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203240

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203240

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				92															
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72															
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61															
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57															
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53															
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49				49															
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46				46															

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203240

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.4	9.0
10°-20°	251.9	23.4
20°-30°	326.5	30.3
30°-40°	242.3	22.5
40°-50°	102.3	9.5
50°-60°	36.3	3.4
60°-70°	14.0	1.3
70°-80°	4.8	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.8	62.8
0°-40°	918.1	85.3
0°-60°	1056.8	98.2
0°-90°	1076.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1076.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1065	
5°	1042	97
15°	899	252
25°	724	326
35°	384	242
45°	126	102
55°	38	36
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P203240

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1065.1
2.5°	1062.1
5°	1042.1
7.5°	1012.9
10°	977.5
12.5°	939.1
15°	899.1
17.5°	854.6
20°	814.6
22.5°	773.1
25°	723.9
27.5°	656.3
30°	576.4
32.5°	482.6
35°	384.2
37.5°	301.2
40°	229.0
42.5°	170.6
45°	126.0
47.5°	92.2
50°	67.6
52.5°	50.7
55°	38.4
57.5°	29.2
60°	23.1
62.5°	16.9
65°	13.8
67.5°	10.8
70°	7.7
72.5°	6.1
75°	4.6
77.5°	3.1
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)