

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202552

Luminaire Tested: **LSR6B40D010BZ EC6B30509730 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509730 6LBSWMH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3277.4 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202552

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202552

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42																			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38																			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35																			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202552

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	5.4
10°-20°	458.4	14.0
20°-30°	607.8	18.5
30°-40°	648.3	19.8
40°-50°	606.0	18.5
50°-60°	462.1	14.1
60°-70°	251.3	7.7
70°-80°	67.4	2.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.5	37.9
0°-40°	1889.8	57.7
0°-60°	2957.8	90.2
0°-90°	3277.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3277.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1895	
5°	1869	175
15°	1634	458
25°	1323	608
35°	1036	648
45°	789	606
55°	520	462
65°	251	251
75°	58	67
85°	0	1
90°	0	



TEST NUMBER: P202552

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1895.2
2.5°	1889.2
5°	1869.1
7.5°	1827.0
10°	1778.8
12.5°	1710.5
15°	1634.2
17.5°	1557.9
20°	1475.6
22.5°	1397.3
25°	1323.0
27.5°	1244.7
30°	1170.5
32.5°	1098.2
35°	1035.9
37.5°	973.7
40°	909.5
42.5°	851.2
45°	789.0
47.5°	720.7
50°	656.5
52.5°	588.2
55°	520.0
57.5°	445.7
60°	377.4
62.5°	313.2
65°	251.0
67.5°	194.7
70°	142.5
72.5°	98.4
75°	58.2
77.5°	26.1
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)