

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203572

Luminaire Tested: **LSR6B40D010BZ EC6B30508035 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203572  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30508035 6LBMMW1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3433.4 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203572

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203572

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203572

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	236.7	6.9
10°-20°	633.9	18.5
20°-30°	851.1	24.8
30°-40°	698.2	20.3
40°-50°	419.3	12.2
50°-60°	278.6	8.1
60°-70°	186.7	5.4
70°-80°	100.5	2.9
80°-90°	28.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1721.7	50.1
0°-40°	2419.9	70.5
0°-60°	3117.8	90.8
0°-90°	3433.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3433.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2562	
5°	2519	237
15°	2259	634
25°	1875	851
35°	1108	698
45°	530	419
55°	308	279
65°	189	187
75°	95	101
85°	24	28
90°	0	



TEST NUMBER: P203572

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2561.9
2.5°	2542.9
5°	2519.3
7.5°	2467.2
10°	2405.6
12.5°	2329.8
15°	2258.8
17.5°	2173.6
20°	2088.3
22.5°	1993.6
25°	1875.2
27.5°	1733.2
30°	1543.8
32.5°	1330.7
35°	1108.1
37.5°	918.7
40°	757.7
42.5°	629.8
45°	530.4
47.5°	449.9
50°	393.0
52.5°	345.7
55°	307.8
57.5°	274.7
60°	246.2
62.5°	213.1
65°	189.4
67.5°	161.0
70°	137.3
72.5°	113.7
75°	94.7
77.5°	75.8
80°	56.8
82.5°	42.6
85°	23.7
87.5°	9.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)