

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203778

Luminaire Tested: **LSR6B40D010BZ EC6B30508035 6LBNWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203778  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30508035 6LBNWH1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2884.0 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203778

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBNWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203778

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBNWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94	94	94		
	2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89	89	87	85	85	89		
	3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83	89	87	85	85	83		
	4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79	85	82	80	80	79		
	5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74	81	78	75	75	74		
	6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70	78	74	71	71	70		
	7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66	74	70	67	67	66		
	8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63	71	67	64	64	63		
	9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60	68	64	61	61	60		
	10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	65	61	58	58	57		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203778

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBNWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	479.3	16.6
10°-20°	921.0	31.9
20°-30°	837.3	29.0
30°-40°	507.5	17.6
40°-50°	115.6	4.0
50°-60°	14.7	0.5
60°-70°	6.6	0.2
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2237.6	77.6
0°-40°	2745.2	95.2
0°-60°	2875.5	99.7
0°-90°	2884.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2884.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5662	
5°	5338	479
15°	3317	921
25°	1816	837
35°	805	508
45°	128	116
55°	15	15
65°	5	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P203778

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBNWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5662.3
2.5°	5593.6
5°	5338.5
7.5°	4926.3
10°	4401.3
12.5°	3856.6
15°	3316.9
17.5°	2826.2
20°	2414.1
22.5°	2080.4
25°	1815.5
27.5°	1579.9
30°	1349.3
32.5°	1079.5
35°	804.7
37.5°	564.3
40°	372.9
42.5°	230.6
45°	127.6
47.5°	58.9
50°	24.5
52.5°	19.6
55°	14.7
57.5°	14.7
60°	9.8
62.5°	9.8
65°	4.9
67.5°	4.9
70°	4.9
72.5°	4.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)