

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202748

Luminaire Tested: **LSR6B40D010BZ EC6B30508035 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508035 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3786.6 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202748

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202748

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202748

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.6	5.8
10°-20°	625.9	16.5
20°-30°	917.7	24.2
30°-40°	955.1	25.2
40°-50°	660.8	17.5
50°-60°	287.7	7.6
60°-70°	88.2	2.3
70°-80°	26.4	0.7
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1764.2	46.6
0°-40°	2719.4	71.8
0°-60°	3667.9	96.9
0°-90°	3786.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3786.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2336	
5°	2326	221
15°	2223	626
25°	2007	918
35°	1546	955
45°	854	661
55°	309	288
65°	83	88
75°	24	26
85°	5	4
90°	0	



TEST NUMBER: P202748

CATALOG NUMBER: LSR6B40D010BZ EC6B30508035 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2335.5
2.5°	2340.4
5°	2325.7
7.5°	2306.1
10°	2281.6
12.5°	2257.0
15°	2222.7
17.5°	2178.5
20°	2129.5
22.5°	2075.5
25°	2006.8
27.5°	1918.5
30°	1805.6
32.5°	1687.9
35°	1545.6
37.5°	1388.6
40°	1207.0
42.5°	1025.5
45°	853.7
47.5°	691.8
50°	549.5
52.5°	417.1
55°	309.1
57.5°	220.8
60°	152.1
62.5°	112.9
65°	83.4
67.5°	63.8
70°	44.2
72.5°	34.3
75°	24.5
77.5°	14.7
80°	9.8
82.5°	4.9
85°	4.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)