

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204896

Luminaire Tested: **LSR6B20D010BZ EC6B10209727 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209727 6LBCSMB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1350.9 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204896

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204896

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																																				
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																																				
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																																				
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																																				
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																																				
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																																				
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																																				
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																																				
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																																				
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204896

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	4.0
10°-20°	153.7	11.4
20°-30°	231.1	17.1
30°-40°	274.2	20.3
40°-50°	271.3	20.1
50°-60°	213.1	15.8
60°-70°	119.5	8.8
70°-80°	33.6	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.7	32.5
0°-40°	712.9	52.8
0°-60°	1197.3	88.6
0°-90°	1350.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1350.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	570	
5°	570	54
15°	545	154
25°	502	231
35°	440	274
45°	354	271
55°	240	213
65°	119	119
75°	29	34
85°	0	1
90°	0	



TEST NUMBER: P204896

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	570.4
2.5°	568.5
5°	569.5
7.5°	564.6
10°	558.8
12.5°	552.0
15°	545.2
17.5°	536.5
20°	524.9
22.5°	513.3
25°	501.7
27.5°	489.1
30°	472.6
32.5°	456.1
35°	439.7
37.5°	420.3
40°	398.0
42.5°	376.7
45°	353.5
47.5°	327.3
50°	300.2
52.5°	269.2
55°	240.2
57.5°	207.3
60°	176.3
62.5°	148.2
65°	119.1
67.5°	93.9
70°	69.7
72.5°	47.5
75°	29.1
77.5°	14.5
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)