

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205021

Luminaire Tested: **LSR6B40D010BZ EC6B30509035 6LBSCMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205021  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30509035 6LBCSMMS1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3722.0 lumens  
Efficiency: N/A  
Efficacy: 89.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205021

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P205021

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50		
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44		
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40		
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36		
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32		
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205021

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.1	4.3
10°-20°	452.0	12.1
20°-30°	660.2	17.7
30°-40°	755.1	20.3
40°-50°	725.7	19.5
50°-60°	560.3	15.1
60°-70°	312.8	8.4
70°-80°	91.0	2.4
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1273.2	34.2
0°-40°	2028.3	54.5
0°-60°	3314.3	89.0
0°-90°	3722.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3722.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1709	
5°	1695	161
15°	1603	452
25°	1435	660
35°	1208	755
45°	946	726
55°	628	560
65°	313	313
75°	79	91
85°	2	4
90°	0	



TEST NUMBER: P205021

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1709.3
2.5°	1709.3
5°	1694.8
7.5°	1687.6
10°	1663.5
12.5°	1634.6
15°	1603.3
17.5°	1572.0
20°	1526.3
22.5°	1490.2
25°	1434.8
27.5°	1379.5
30°	1324.1
32.5°	1268.7
35°	1208.5
37.5°	1148.3
40°	1078.5
42.5°	1015.9
45°	946.1
47.5°	866.7
50°	792.0
52.5°	710.2
55°	628.3
57.5°	544.1
60°	464.6
62.5°	385.2
65°	313.0
67.5°	245.6
70°	183.0
72.5°	127.6
75°	79.4
77.5°	40.9
80°	14.4
82.5°	4.8
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)