

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204402

Luminaire Tested: **LSR6B40D010BZ EC6B30509035 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509035 6LBSGPH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3457.8 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204402

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204402

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76																			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66																			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57																			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50																			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45																			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32																			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204402

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.2	4.4
10°-20°	424.5	12.3
20°-30°	619.1	17.9
30°-40°	706.0	20.4
40°-50°	677.2	19.6
50°-60°	518.6	15.0
60°-70°	284.6	8.2
70°-80°	75.7	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.7	34.6
0°-40°	1900.7	55.0
0°-60°	3096.5	89.5
0°-90°	3457.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3457.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1606	
5°	1594	151
15°	1506	424
25°	1345	619
35°	1129	706
45°	880	677
55°	581	519
65°	286	285
75°	66	76
85°	0	1
90°	0	



TEST NUMBER: P204402

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1606.0
2.5°	1601.9
5°	1593.6
7.5°	1581.1
10°	1564.5
12.5°	1535.5
15°	1506.4
17.5°	1473.2
20°	1435.9
22.5°	1390.2
25°	1344.6
27.5°	1298.9
30°	1240.8
32.5°	1186.9
35°	1128.8
37.5°	1070.7
40°	1012.6
42.5°	950.3
45°	879.8
47.5°	809.2
50°	734.5
52.5°	655.7
55°	581.0
57.5°	506.3
60°	427.4
62.5°	352.7
65°	286.3
67.5°	219.9
70°	161.8
72.5°	107.9
75°	66.4
77.5°	29.0
80°	8.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)