

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203854

Luminaire Tested: **LSR6B20D010BZ EC6B10208030 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208030 6LBNGPH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1025.0 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203854

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203854

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203854

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	11.0
10°-20°	278.2	27.1
20°-30°	337.1	32.9
30°-40°	229.7	22.4
40°-50°	54.7	5.3
50°-60°	8.6	0.8
60°-70°	3.2	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.0	71.0
0°-40°	957.7	93.4
0°-60°	1021.0	99.6
0°-90°	1025.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1246	
5°	1211	113
15°	996	278
25°	736	337
35°	367	230
45°	58	55
55°	9	9
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203854

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1246.0
2.5°	1239.0
5°	1210.9
7.5°	1173.5
10°	1119.8
12.5°	1059.0
15°	995.9
17.5°	930.4
20°	864.9
22.5°	799.5
25°	736.4
27.5°	677.9
30°	593.8
32.5°	483.9
35°	367.0
37.5°	261.8
40°	173.0
42.5°	107.5
45°	58.4
47.5°	30.4
50°	16.4
52.5°	11.7
55°	9.4
57.5°	7.0
60°	4.7
62.5°	4.7
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)