

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202515

Luminaire Tested: **LSR6B20D010BZ EC6B10208030 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208030 6LBSWMH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2134.1 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202515
CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202515

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202515

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.2	5.4
10°-20°	298.5	14.0
20°-30°	395.8	18.5
30°-40°	422.1	19.8
40°-50°	394.6	18.5
50°-60°	300.9	14.1
60°-70°	163.7	7.7
70°-80°	43.9	2.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.4	37.9
0°-40°	1230.6	57.7
0°-60°	1926.1	90.2
0°-90°	2134.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2134.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1234	
5°	1217	114
15°	1064	298
25°	862	396
35°	675	422
45°	514	395
55°	339	301
65°	163	164
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P202515

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1234.1
2.5°	1230.2
5°	1217.1
7.5°	1189.7
10°	1158.3
12.5°	1113.8
15°	1064.2
17.5°	1014.5
20°	960.9
22.5°	909.9
25°	861.5
27.5°	810.5
30°	762.2
32.5°	715.1
35°	674.6
37.5°	634.1
40°	592.2
42.5°	554.3
45°	513.8
47.5°	469.3
50°	427.5
52.5°	383.0
55°	338.6
57.5°	290.2
60°	245.8
62.5°	203.9
65°	163.4
67.5°	126.8
70°	92.8
72.5°	64.1
75°	37.9
77.5°	17.0
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)