

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205191

Luminaire Tested: **LSR6B20D010BZ EC6B10208030 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205191  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10208030 6LBWLI1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2059.4 lumens  
Efficiency: N/A  
Efficacy: 99.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205191

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWL11

### Luminous Intensity Polar Plot





TEST NUMBER: P205191

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205191

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.1	6.0
10°-20°	373.1	18.1
20°-30°	562.4	27.3
30°-40°	575.6	27.9
40°-50°	335.3	16.3
50°-60°	77.0	3.7
60°-70°	9.5	0.5
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1059.5	51.4
0°-40°	1635.1	79.4
0°-60°	2047.5	99.4
0°-90°	2059.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2059.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1287	
5°	1294	124
15°	1322	373
25°	1233	562
35°	934	576
45°	432	335
55°	75	77
65°	7	9
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205191

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1286.6
2.5°	1284.3
5°	1293.6
7.5°	1302.9
10°	1314.6
12.5°	1316.9
15°	1321.6
17.5°	1316.9
20°	1305.3
22.5°	1267.9
25°	1232.9
27.5°	1176.8
30°	1104.5
32.5°	1029.7
35°	934.0
37.5°	826.6
40°	707.5
42.5°	574.4
45°	432.0
47.5°	301.2
50°	198.5
52.5°	126.1
55°	74.7
57.5°	39.7
60°	21.0
62.5°	11.7
65°	7.0
67.5°	7.0
70°	4.7
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)