

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203470

Luminaire Tested: **LSR6B40D010BZ EC6B30508040 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508040 6LBMB1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1884.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203470

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P203470

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																																			
	2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																																			
	3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																																			
	4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76																																			
	5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72																																			
	6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																																			
	7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63																																			
	8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																																			
	9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																																			
	10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203470

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.2	11.4
10°-20°	531.0	28.2
20°-30°	639.6	33.9
30°-40°	404.6	21.5
40°-50°	92.6	4.9
50°-60°	1.0	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1385.8	73.6
0°-40°	1790.4	95.0
0°-60°	1884.0	100.0
0°-90°	1884.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1884.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2372	
5°	2318	215
15°	1894	531
25°	1417	640
35°	638	405
45°	102	93
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203470

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2371.8
2.5°	2362.1
5°	2318.2
7.5°	2235.4
10°	2133.2
12.5°	2011.4
15°	1894.5
17.5°	1782.5
20°	1665.6
22.5°	1548.7
25°	1417.2
27.5°	1261.4
30°	1071.4
32.5°	857.2
35°	638.0
37.5°	452.9
40°	306.8
42.5°	189.9
45°	102.3
47.5°	43.8
50°	9.7
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)