

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204995

Luminaire Tested: **LSR6B20D010BZ EC6B10209030 6LBSCMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209030 6LBCSMMS1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1790.4 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204995

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P204995

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204995

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	4.3
10°-20°	217.4	12.1
20°-30°	317.6	17.7
30°-40°	363.2	20.3
40°-50°	349.1	19.5
50°-60°	269.6	15.1
60°-70°	150.4	8.4
70°-80°	43.8	2.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.5	34.2
0°-40°	975.7	54.5
0°-60°	1594.3	89.0
0°-90°	1790.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1790.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	822	
5°	815	77
15°	771	217
25°	690	318
35°	581	363
45°	455	349
55°	302	270
65°	150	150
75°	38	44
85°	1	2
90°	0	



TEST NUMBER: P204995

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	822.2
2.5°	822.2
5°	815.3
7.5°	811.8
10°	800.2
12.5°	786.3
15°	771.3
17.5°	756.2
20°	734.2
22.5°	716.8
25°	690.2
27.5°	663.6
30°	636.9
32.5°	610.3
35°	581.3
37.5°	552.4
40°	518.8
42.5°	488.7
45°	455.1
47.5°	416.9
50°	381.0
52.5°	341.6
55°	302.3
57.5°	261.7
60°	223.5
62.5°	185.3
65°	150.5
67.5°	118.1
70°	88.0
72.5°	61.4
75°	38.2
77.5°	19.7
80°	6.9
82.5°	2.3
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)