

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205503

Luminaire Tested: **LSR6B20D010BZ EC6B10209030 6LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205503  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209030 6LBMGPH1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 971.3 lumens  
Efficiency: N/A  
Efficacy: 46.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205503

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205503

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205503

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.0	9.6
10°-20°	241.3	24.8
20°-30°	307.4	31.6
30°-40°	217.2	22.4
40°-50°	79.3	8.2
50°-60°	22.0	2.3
60°-70°	8.0	0.8
70°-80°	2.9	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	641.7	66.1
0°-40°	858.9	88.4
0°-60°	960.2	98.9
0°-90°	971.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1012	
5°	994	93
15°	859	241
25°	683	307
35°	345	217
45°	96	79
55°	24	22
65°	8	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P205503

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1012.2
2.5°	1008.2
5°	994.5
7.5°	967.0
10°	937.6
12.5°	898.4
15°	859.2
17.5°	819.9
20°	780.7
22.5°	733.6
25°	682.6
27.5°	612.0
30°	533.5
32.5°	439.4
35°	345.2
37.5°	262.8
40°	192.2
42.5°	139.3
45°	96.1
47.5°	64.7
50°	43.2
52.5°	29.4
55°	23.5
57.5°	17.7
60°	13.7
62.5°	9.8
65°	7.8
67.5°	5.9
70°	3.9
72.5°	3.9
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)