

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203551

Luminaire Tested: **LSR6B20D010BZ EC6B10209030 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209030 6LBMMW1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1396.1 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203551

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203551

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203551

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	6.9
10°-20°	257.8	18.5
20°-30°	346.1	24.8
30°-40°	283.9	20.3
40°-50°	170.5	12.2
50°-60°	113.3	8.1
60°-70°	75.9	5.4
70°-80°	40.9	2.9
80°-90°	11.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.1	50.1
0°-40°	984.0	70.5
0°-60°	1267.8	90.8
0°-90°	1396.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1396.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	1024	96
15°	918	258
25°	762	346
35°	451	284
45°	216	170
55°	125	113
65°	77	76
75°	38	41
85°	10	12
90°	0	



TEST NUMBER: P203551

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1041.7
2.5°	1034.0
5°	1024.4
7.5°	1003.2
10°	978.2
12.5°	947.4
15°	918.5
17.5°	883.8
20°	849.2
22.5°	810.7
25°	762.5
27.5°	704.8
30°	627.7
32.5°	541.1
35°	450.6
37.5°	373.6
40°	308.1
42.5°	256.1
45°	215.7
47.5°	182.9
50°	159.8
52.5°	140.6
55°	125.2
57.5°	111.7
60°	100.1
62.5°	86.7
65°	77.0
67.5°	65.5
70°	55.8
72.5°	46.2
75°	38.5
77.5°	30.8
80°	23.1
82.5°	17.3
85°	9.6
87.5°	3.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)