

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203992

Luminaire Tested: **LSR6B40D010BZ EC6B30509050 6LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509050 6LBNB1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1589.2 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.83
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203992

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P203992

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94						94													
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88						88													
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82						82													
4	98	91	86	82	96	90	85	81	88	84	80	86	82	79	84	81	78	77						77													
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72						72													
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67						67													
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63						63													
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60						60													
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	58	56						56													
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53						53													

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203992

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	12.8
10°-20°	442.3	27.8
20°-30°	519.8	32.7
30°-40°	357.9	22.5
40°-50°	66.3	4.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.1	73.3
0°-40°	1523.0	95.8
0°-60°	1589.2	100.0
0°-90°	1589.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1589.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2340	
5°	2227	203
15°	1574	442
25°	1136	520
35°	574	358
45°	67	66
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203992

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2339.6
2.5°	2318.8
5°	2227.2
7.5°	2098.1
10°	1919.1
12.5°	1740.1
15°	1573.6
17.5°	1432.1
20°	1319.7
22.5°	1223.9
25°	1136.5
27.5°	1049.1
30°	932.5
32.5°	766.0
35°	574.5
37.5°	399.6
40°	253.9
42.5°	141.5
45°	66.6
47.5°	20.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)