

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204715

Luminaire Tested: **LSR6B40D010BZ EC6B30509050 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509050 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3954.3 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204715

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204715

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204715

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	3.8
10°-20°	430.3	10.9
20°-30°	648.1	16.4
30°-40°	771.1	19.5
40°-50°	769.7	19.5
50°-60°	626.0	15.8
60°-70°	385.1	9.7
70°-80°	149.2	3.8
80°-90°	23.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1229.3	31.1
0°-40°	2000.4	50.6
0°-60°	3396.1	85.9
0°-90°	3954.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3954.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1593	
5°	1588	151
15°	1528	430
25°	1410	648
35°	1235	771
45°	1000	770
55°	700	626
65°	387	385
75°	136	149
85°	19	24
90°	0	



TEST NUMBER: P204715

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1593.2
2.5°	1595.6
5°	1588.5
7.5°	1579.2
10°	1567.4
12.5°	1546.3
15°	1527.6
17.5°	1499.5
20°	1469.0
22.5°	1440.9
25°	1410.5
27.5°	1368.3
30°	1326.1
32.5°	1286.3
35°	1234.7
37.5°	1178.5
40°	1127.0
42.5°	1063.7
45°	1000.4
47.5°	932.5
50°	859.9
52.5°	784.9
55°	700.5
57.5°	618.5
60°	538.9
62.5°	461.6
65°	386.6
67.5°	316.3
70°	250.7
72.5°	189.8
75°	135.9
77.5°	89.0
80°	53.9
82.5°	32.8
85°	18.7
87.5°	9.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)