

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204198

Luminaire Tested: **LSR6B40D010BZ EC6B30509050 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509050 6LBSH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3791.7 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204198

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204198

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204198

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.7	4.9
10°-20°	504.9	13.3
20°-30°	701.1	18.5
30°-40°	765.1	20.2
40°-50°	713.7	18.8
50°-60°	541.8	14.3
60°-70°	296.6	7.8
70°-80°	81.6	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1391.7	36.7
0°-40°	2156.9	56.9
0°-60°	3412.4	90.0
0°-90°	3791.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3791.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1983	
5°	1966	186
15°	1799	505
25°	1524	701
35°	1223	765
45°	927	714
55°	605	542
65°	296	297
75°	71	82
85°	0	1
90°	0	



TEST NUMBER: P204198

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1983.1
2.5°	1983.1
5°	1966.4
7.5°	1941.3
10°	1903.7
12.5°	1853.6
15°	1799.4
17.5°	1732.6
20°	1669.9
22.5°	1594.8
25°	1523.8
27.5°	1452.9
30°	1373.5
32.5°	1298.4
35°	1223.2
37.5°	1148.1
40°	1077.1
42.5°	1002.0
45°	926.8
47.5°	851.7
50°	768.2
52.5°	688.9
55°	605.4
57.5°	526.0
60°	446.7
62.5°	367.4
65°	296.4
67.5°	229.6
70°	171.2
72.5°	116.9
75°	71.0
77.5°	33.4
80°	8.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)