

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203964

Luminaire Tested: **LSR6B20D010BZ EC6B10209035 6LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209035 6LBNB1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 770.7 lumens
Efficiency: N/A
Efficacy: 37.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.83
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203964

CATALOG NUMBER: LSR6B20D010BZ EC6B10209035 6LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P203964

CATALOG NUMBER: LSR6B20D010BZ EC6B10209035 6LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																																				
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88																																				
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82																																				
4	98	91	86	82	96	90	85	81	88	84	80	86	82	79	84	81	78	77																																				
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																																				
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67																																				
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63																																				
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60																																				
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	58	56																																				
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203964

CATALOG NUMBER: LSR6B20D010BZ EC6B10209035 6LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.4	12.8
10°-20°	214.5	27.8
20°-30°	252.1	32.7
30°-40°	173.6	22.5
40°-50°	32.1	4.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.0	73.3
0°-40°	738.6	95.8
0°-60°	770.7	100.0
0°-90°	770.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1135	
5°	1080	98
15°	763	215
25°	551	252
35°	279	174
45°	32	32
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203964

CATALOG NUMBER: LSR6B20D010BZ EC6B10209035 6LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1134.6
2.5°	1124.5
5°	1080.1
7.5°	1017.5
10°	930.7
12.5°	843.9
15°	763.1
17.5°	694.5
20°	640.0
22.5°	593.6
25°	551.2
27.5°	508.8
30°	452.2
32.5°	371.5
35°	278.6
37.5°	193.8
40°	123.2
42.5°	68.6
45°	32.3
47.5°	10.1
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)