

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205396

Luminaire Tested: **LSR6B20D010BZ EC6B10208040 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208040 6LBSLI1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2275.8 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205396

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205396

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205396

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	5.8
10°-20°	336.9	14.8
20°-30°	429.6	18.9
30°-40°	445.5	19.6
40°-50°	410.5	18.0
50°-60°	308.8	13.6
60°-70°	166.7	7.3
70°-80°	44.7	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.9	39.5
0°-40°	1344.4	59.1
0°-60°	2063.8	90.7
0°-90°	2275.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2275.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1436	
5°	1414	132
15°	1202	337
25°	933	430
35°	711	446
45°	534	411
55°	346	309
65°	167	167
75°	39	45
85°	0	1
90°	0	



TEST NUMBER: P205396

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1436.2
2.5°	1431.3
5°	1414.4
7.5°	1383.0
10°	1327.4
12.5°	1271.8
15°	1201.6
17.5°	1136.4
20°	1068.7
22.5°	998.5
25°	933.3
27.5°	870.4
30°	812.4
32.5°	759.2
35°	710.8
37.5°	664.9
40°	621.4
42.5°	575.4
45°	534.3
47.5°	488.4
50°	442.5
52.5°	394.1
55°	345.7
57.5°	297.4
60°	251.4
62.5°	207.9
65°	166.8
67.5°	128.1
70°	94.3
72.5°	65.3
75°	38.7
77.5°	16.9
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)