

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274422

Luminaire Tested: **LD6B10DE010W2N2765 EU6B1020W2N902765 6LBCS0MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35143)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBCS0MB
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, CAST SHALLOW WITH MATTE BLACK FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 880.1 lumens
Efficiency: N/A
Efficacy: 62.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274422

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBCS0MB

Luminous Intensity Polar Plot





TEST NUMBER: P274422

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBCS0MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24250
5°	24297
10°	24121
15°	23991
20°	23744
25°	23532
30°	23195
35°	22818
40°	22083
45°	21248
50°	19853
55°	17801
60°	14979
65°	11979
70°	8660
75°	4764
80°	939
85°	0



TEST NUMBER: P274422

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBCS0MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	4.0
10°-20°	100.1	11.4
20°-30°	150.6	17.1
30°-40°	178.6	20.3
40°-50°	176.8	20.1
50°-60°	138.8	15.8
60°-70°	77.8	8.8
70°-80°	21.9	2.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.9	32.5
0°-40°	464.5	52.8
0°-60°	780.1	88.6
0°-90°	880.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	372	
5°	371	35
15°	355	100
25°	327	151
35°	286	179
45°	230	177
55°	156	139
65°	78	78
75°	19	22
85°	0	0
90°	0	



TEST NUMBER: P274422

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBCS0MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	371.7
2.5°	370.4
5°	371.0
7.5°	367.9
10°	364.1
12.5°	359.7
15°	355.2
17.5°	349.6
20°	342.0
22.5°	334.4
25°	326.9
27.5°	318.7
30°	307.9
32.5°	297.2
35°	286.5
37.5°	273.9
40°	259.3
42.5°	245.5
45°	230.3
47.5°	213.3
50°	195.6
52.5°	175.4
55°	156.5
57.5°	135.0
60°	114.8
62.5°	96.5
65°	77.6
67.5°	61.2
70°	45.4
72.5°	30.9
75°	18.9
77.5°	9.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)