

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202826

Luminaire Tested: **LSR6B20D010BZ EC6B10208040 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202826  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10208040 6LBWWH1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1930.0 lumens  
Efficiency: N/A  
Efficacy: 92.8 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202826

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202826

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202826

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.2	6.0
10°-20°	342.6	17.8
20°-30°	515.8	26.7
30°-40°	527.4	27.3
40°-50°	320.3	16.6
50°-60°	90.2	4.7
60°-70°	13.7	0.7
70°-80°	4.4	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.7	50.4
0°-40°	1501.0	77.8
0°-60°	1911.5	99.0
0°-90°	1930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1199	
5°	1204	115
15°	1213	343
25°	1126	516
35°	855	527
45°	412	320
55°	90	90
65°	12	14
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P202826

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1198.7
2.5°	1198.7
5°	1203.6
7.5°	1210.8
10°	1210.8
12.5°	1215.7
15°	1213.3
17.5°	1208.4
20°	1191.5
22.5°	1167.2
25°	1126.1
27.5°	1080.1
30°	1017.1
32.5°	942.0
35°	854.9
37.5°	758.0
40°	646.6
42.5°	530.3
45°	411.7
47.5°	305.1
50°	215.5
52.5°	145.3
55°	89.6
57.5°	53.3
60°	26.6
62.5°	17.0
65°	12.1
67.5°	9.7
70°	7.3
72.5°	4.8
75°	4.8
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)