

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205300

Luminaire Tested: **LSR6B20D010BZ EC6B10209040 6LBNI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205300  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209040 6LBNLI1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1405.8 lumens  
Efficiency: N/A  
Efficacy: 67.6 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205300

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBNLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205300

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBNLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72		
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68		
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205300

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBNLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	266.1	18.9
10°-20°	477.7	34.0
20°-30°	386.2	27.5
30°-40°	222.5	15.8
40°-50°	47.0	3.3
50°-60°	4.1	0.3
60°-70°	2.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.0	80.4
0°-40°	1352.5	96.2
0°-60°	1403.6	99.8
0°-90°	1405.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1405.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3201	
5°	2982	266
15°	1735	478
25°	833	386
35°	353	222
45°	51	47
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P205300

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBNLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3200.8
2.5°	3162.3
5°	2981.9
7.5°	2722.4
10°	2404.1
12.5°	2077.8
15°	1735.2
17.5°	1404.8
20°	1163.6
22.5°	979.1
25°	833.1
27.5°	709.5
30°	598.0
32.5°	474.3
35°	352.7
37.5°	245.3
40°	160.1
42.5°	97.3
45°	50.7
47.5°	20.3
50°	6.1
52.5°	6.1
55°	4.1
57.5°	4.1
60°	2.0
62.5°	2.0
65°	2.0
67.5°	2.0
70°	2.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)