

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204792

Luminaire Tested: **LSR6B20D010BZ EC6B10209050 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209050 6LBCSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1950.8 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204792

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204792

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204792

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	3.9
10°-20°	214.9	11.0
20°-30°	323.3	16.6
30°-40°	383.1	19.6
40°-50°	381.3	19.5
50°-60°	307.4	15.8
60°-70°	185.9	9.5
70°-80°	69.1	3.5
80°-90°	10.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.7	31.5
0°-40°	996.8	51.1
0°-60°	1685.5	86.4
0°-90°	1950.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1950.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	797	
5°	793	75
15°	761	215
25°	702	323
35°	614	383
45°	496	381
55°	343	307
65°	187	186
75°	63	69
85°	8	10
90°	0	



TEST NUMBER: P204792

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	796.8
2.5°	796.8
5°	793.2
7.5°	790.8
10°	783.8
12.5°	771.9
15°	761.3
17.5°	749.5
20°	735.3
22.5°	721.1
25°	702.2
27.5°	682.1
30°	659.6
32.5°	638.4
35°	613.5
37.5°	587.5
40°	556.8
42.5°	527.2
45°	496.5
47.5°	462.2
50°	424.4
52.5°	385.4
55°	342.8
57.5°	305.0
60°	262.4
62.5°	224.6
65°	186.8
67.5°	151.3
70°	118.2
72.5°	88.7
75°	62.7
77.5°	40.2
80°	23.6
82.5°	14.2
85°	8.3
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)