

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205006

Luminaire Tested: **LSR6B30D010BZ EC6B30509024 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509024 6LBCSMMS1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2196.2 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205006

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205006

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205006

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	4.3
10°-20°	266.7	12.1
20°-30°	389.5	17.7
30°-40°	445.5	20.3
40°-50°	428.2	19.5
50°-60°	330.6	15.1
60°-70°	184.6	8.4
70°-80°	53.7	2.4
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.3	34.2
0°-40°	1196.8	54.5
0°-60°	1955.6	89.0
0°-90°	2196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2196.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1008	
5°	1000	95
15°	946	267
25°	847	390
35°	713	446
45°	558	428
55°	371	331
65°	185	185
75°	47	54
85°	1	2
90°	0	



TEST NUMBER: P205006

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1008.5
2.5°	1008.5
5°	1000.0
7.5°	995.8
10°	981.6
12.5°	964.5
15°	946.0
17.5°	927.6
20°	900.6
22.5°	879.3
25°	846.6
27.5°	813.9
30°	781.3
32.5°	748.6
35°	713.1
37.5°	677.6
40°	636.4
42.5°	599.4
45°	558.3
47.5°	511.4
50°	467.3
52.5°	419.0
55°	370.7
57.5°	321.0
60°	274.2
62.5°	227.3
65°	184.7
67.5°	144.9
70°	108.0
72.5°	75.3
75°	46.9
77.5°	24.1
80°	8.5
82.5°	2.8
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)