

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274386

Luminaire Tested: **LD6B15DE010W2N2765 EU6B1020W2N902765 6LBM0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35125)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBM0H
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1099.7 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274386

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P274386

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71001
5°	69734
10°	66168
15°	62051
20°	57785
25°	53247
30°	44364
35°	31268
40°	19929
45°	11884
50°	7013
55°	4470
60°	3079
65°	2177
70°	1507
75°	1185
80°	601
85°	0



TEST NUMBER: P274386

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	9.0
10°-20°	257.4	23.4
20°-30°	333.6	30.3
30°-40°	247.6	22.5
40°-50°	104.5	9.5
50°-60°	37.1	3.4
60°-70°	14.3	1.3
70°-80°	5.0	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.5	62.8
0°-40°	938.1	85.3
0°-60°	1079.8	98.2
0°-90°	1099.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1099.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1088	
5°	1065	100
15°	919	257
25°	740	334
35°	393	248
45°	129	105
55°	39	37
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P274386

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBM0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1088.3
2.5°	1085.2
5°	1064.8
7.5°	1034.9
10°	998.8
12.5°	959.5
15°	918.7
17.5°	873.2
20°	832.3
22.5°	789.9
25°	739.7
27.5°	670.6
30°	588.9
32.5°	493.1
35°	392.6
37.5°	307.8
40°	234.0
42.5°	174.3
45°	128.8
47.5°	94.2
50°	69.1
52.5°	51.8
55°	39.3
57.5°	29.8
60°	23.6
62.5°	17.3
65°	14.1
67.5°	11.0
70°	7.9
72.5°	6.3
75°	4.7
77.5°	3.1
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)