

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204077

Luminaire Tested: **LSR6B30D010BZ EC6B30509024 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509024 6LBNMW1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1541.2 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204077

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204077

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204077

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	7.6
10°-20°	311.1	20.2
20°-30°	415.4	27.0
30°-40°	335.1	21.7
40°-50°	160.6	10.4
50°-60°	95.2	6.2
60°-70°	63.3	4.1
70°-80°	33.9	2.2
80°-90°	9.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.8	54.8
0°-40°	1178.9	76.5
0°-60°	1434.7	93.1
0°-90°	1541.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1541.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1264	
5°	1249	117
15°	1107	311
25°	909	415
35°	536	335
45°	198	161
55°	105	95
65°	64	63
75°	32	34
85°	7	9
90°	0	



TEST NUMBER: P204077

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1264.0
2.5°	1264.0
5°	1249.3
7.5°	1224.8
10°	1190.5
12.5°	1153.8
15°	1107.2
17.5°	1063.1
20°	1014.1
22.5°	962.7
25°	908.8
27.5°	852.5
30°	771.6
32.5°	658.9
35°	536.5
37.5°	423.8
40°	328.2
42.5°	254.8
45°	198.4
47.5°	156.8
50°	132.3
52.5°	117.6
55°	105.3
57.5°	95.5
60°	83.3
62.5°	73.5
65°	63.7
67.5°	53.9
70°	46.5
72.5°	39.2
75°	31.8
77.5°	24.5
80°	19.6
82.5°	14.7
85°	7.3
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)