

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274374

Luminaire Tested: **LD6B15DE010W2N2765 EU6B1020W2N902765 6LBN0H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P274374  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1808-906-17)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBN0H  
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH HAZE FINISH  
Light Source: W2N 2700K-6500K CCT TUNING RANGE  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 947.1 lumens  
Efficiency: N/A  
Efficacy: 43.0 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.77  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 22  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P274374

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBN0H

### Luminous Intensity Polar Plot





TEST NUMBER: P274374

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBN0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88	88	88	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83	83	83	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77	77	77	77
5	94	86	81	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73	73	73	73
6	90	81	75	71	88	80	75	71	79	74	71	78	73	70	76	73	70	68	68	68	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	73	69	66	64	64	64	64
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61	61	61	61
9	78	69	63	59	77	68	63	59	67	63	59	67	62	59	66	62	59	58	58	58	58
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	55	55	55	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	80624
5°	77036
10°	68892
15°	59524
20°	49652
25°	40333
30°	30536
35°	18163
40°	8974
45°	3543
50°	878
55°	564
60°	329
65°	195
70°	240
75°	0
80°	0
85°	0



TEST NUMBER: P274374

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBN0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.3	13.6
10°-20°	291.0	30.7
20°-30°	304.4	32.1
30°-40°	174.2	18.4
40°-50°	40.8	4.3
50°-60°	5.7	0.6
60°-70°	2.0	0.2
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.7	76.4
0°-40°	897.9	94.8
0°-60°	944.4	99.7
0°-90°	947.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1471	
5°	1400	128
15°	1049	291
25°	667	304
35°	271	174
45°	46	41
55°	6	6
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P274374

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBN0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1470.7
2.5°	1451.5
5°	1399.9
7.5°	1323.2
10°	1237.6
12.5°	1146.2
15°	1048.8
17.5°	947.0
20°	851.1
22.5°	758.2
25°	666.8
27.5°	581.2
30°	482.4
32.5°	373.2
35°	271.4
37.5°	188.8
40°	125.4
42.5°	79.7
45°	45.7
47.5°	23.6
50°	10.3
52.5°	8.9
55°	5.9
57.5°	4.4
60°	3.0
62.5°	3.0
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)