

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274381

Luminaire Tested: **LD6B20DE010W2N2765 EU6B1020W2N902765 6LBM0LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P274381  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35220)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBM0LI  
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH SPECULAR FINISH  
Light Source: W2N 2700K-6500K CCT TUNING RANGE  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1655.2 lumens  
Efficiency: N/A  
Efficacy: 59.1 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.84  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P274381

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P274381

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	84	80	78	76			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59			
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	138565
5°	137214
10°	129394
15°	116416
20°	101510
25°	86317
30°	67868
35°	42036
40°	21317
45°	8534
50°	2913
55°	1092
60°	835
65°	494
70°	305
75°	403
80°	0
85°	0



TEST NUMBER: P274381

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.4	11.8
10°-20°	479.5	29.0
20°-30°	544.8	32.9
30°-40°	336.7	20.3
40°-50°	83.1	5.0
50°-60°	11.0	0.7
60°-70°	3.7	0.2
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1219.7	73.7
0°-40°	1556.3	94.0
0°-60°	1650.4	99.7
0°-90°	1655.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1655.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2124	
5°	2095	195
15°	1724	479
25°	1199	545
35°	528	337
45°	92	83
55°	10	11
65°	3	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P274381

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2123.9
2.5°	2117.5
5°	2095.2
7.5°	2039.4
10°	1953.2
12.5°	1844.8
15°	1723.6
17.5°	1591.3
20°	1462.1
22.5°	1329.8
25°	1199.1
27.5°	1061.9
30°	900.9
32.5°	717.5
35°	527.8
37.5°	374.7
40°	250.3
42.5°	156.3
45°	92.5
47.5°	52.6
50°	28.7
52.5°	14.4
55°	9.6
57.5°	8.0
60°	6.4
62.5°	4.8
65°	3.2
67.5°	3.2
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)