

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202532

Luminaire Tested: **LSR6B30D010BZ EC6B30509024 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509024 6LBSWMH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2244.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202532

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202532

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42																			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38																			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35																			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202532

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	5.4
10°-20°	313.8	14.0
20°-30°	416.2	18.5
30°-40°	443.9	19.8
40°-50°	414.9	18.5
50°-60°	316.4	14.1
60°-70°	172.1	7.7
70°-80°	46.2	2.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.1	37.9
0°-40°	1293.9	57.7
0°-60°	2025.2	90.2
0°-90°	2244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2244.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1298	
5°	1280	120
15°	1119	314
25°	906	416
35°	709	444
45°	540	415
55°	356	316
65°	172	172
75°	40	46
85°	0	1
90°	0	



TEST NUMBER: P202532

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1297.7
2.5°	1293.5
5°	1279.8
7.5°	1250.9
10°	1217.9
12.5°	1171.2
15°	1119.0
17.5°	1066.7
20°	1010.4
22.5°	956.8
25°	905.9
27.5°	852.3
30°	801.4
32.5°	751.9
35°	709.3
37.5°	666.7
40°	622.7
42.5°	582.8
45°	540.2
47.5°	493.5
50°	449.5
52.5°	402.8
55°	356.0
57.5°	305.2
60°	258.4
62.5°	214.4
65°	171.8
67.5°	133.3
70°	97.6
72.5°	67.4
75°	39.9
77.5°	17.9
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)