

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203660

Luminaire Tested: **LSR6B30D010BZ EC6B30508027 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508027 6LBNH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1778.0 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203660

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203660

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93	93																																		
	2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	87																																		
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81																																		
	4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75	75																																		
	5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70	70																																		
	6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65	65																																		
	7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61	61																																		
	8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58																																		
	9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54	54																																		
	10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51	51																																		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203660

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.0	11.5
10°-20°	488.8	27.5
20°-30°	560.0	31.5
30°-40°	376.2	21.2
40°-50°	107.5	6.0
50°-60°	26.3	1.5
60°-70°	10.0	0.6
70°-80°	3.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1253.7	70.5
0°-40°	1629.9	91.7
0°-60°	1763.7	99.2
0°-90°	1778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1778.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2279	
5°	2214	205
15°	1754	489
25°	1222	560
35°	600	376
45°	123	108
55°	29	26
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P203660

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2279.2
2.5°	2263.0
5°	2214.4
7.5°	2126.8
10°	2019.8
12.5°	1883.7
15°	1754.0
17.5°	1617.8
20°	1481.6
22.5°	1352.0
25°	1222.3
27.5°	1102.3
30°	962.9
32.5°	778.1
35°	599.8
37.5°	437.7
40°	301.5
42.5°	197.8
45°	123.2
47.5°	74.6
50°	45.4
52.5°	35.7
55°	29.2
57.5°	22.7
60°	16.2
62.5°	13.0
65°	9.7
67.5°	6.5
70°	6.5
72.5°	3.2
75°	3.2
77.5°	3.2
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)