

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204381

Luminaire Tested: **LSR6B30D010BZ EC6B30508027 6LBSGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204381  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508027 6LBSGPH1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2701.0 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204381

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBSGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204381

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBSGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66	66	66	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50	50	50	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45	45	45	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40	40	40	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36	36	36	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32	32	32	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30	30	30	30

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204381

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBSGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.1	4.4
10°-20°	331.5	12.3
20°-30°	483.6	17.9
30°-40°	551.4	20.4
40°-50°	528.9	19.6
50°-60°	405.1	15.0
60°-70°	222.3	8.2
70°-80°	59.1	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.2	34.6
0°-40°	1484.6	55.0
0°-60°	2418.7	89.5
0°-90°	2701.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2701.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1254	
5°	1245	118
15°	1177	332
25°	1050	484
35°	882	551
45°	687	529
55°	454	405
65°	224	222
75°	52	59
85°	0	1
90°	0	



TEST NUMBER: P204381

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBSGPH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1254.5
2.5°	1251.2
5°	1244.7
7.5°	1235.0
10°	1222.1
12.5°	1199.4
15°	1176.7
17.5°	1150.7
20°	1121.6
22.5°	1085.9
25°	1050.3
27.5°	1014.6
30°	969.2
32.5°	927.1
35°	881.7
37.5°	836.3
40°	790.9
42.5°	742.3
45°	687.2
47.5°	632.1
50°	573.7
52.5°	512.2
55°	453.8
57.5°	395.5
60°	333.9
62.5°	275.5
65°	223.7
67.5°	171.8
70°	126.4
72.5°	84.3
75°	51.9
77.5°	22.7
80°	6.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)