

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179745

Luminaire Tested: **LDA6A65930D010TE LARH20SP 6LAL1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26678)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65930D010TE LARH20SP 6LAL1LI
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4241.8 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.45
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 78
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179745

CATALOG NUMBER: LDA6A65930D010TE LARH20SP 6LAL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179745

CATALOG NUMBER: LDA6A65930D010TE LARH20SP 6LAL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	93	93	93	93
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90	90	90	90
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	89	88	86	86	86	86
5	101	94	90	87	99	94	90	87	92	89	86	91	88	85	89	87	85	83	83	83	83
6	97	91	87	84	96	90	86	83	89	85	83	88	85	82	87	84	82	81	81	81	81
7	95	88	84	80	93	87	83	80	86	83	80	85	82	80	84	81	79	78	78	78	78
8	92	85	81	78	91	84	80	78	83	80	77	83	79	77	82	79	77	76	76	76	76
9	89	82	78	75	88	82	78	75	81	77	75	80	77	75	80	77	74	73	73	73	73
10	87	80	75	73	86	79	75	73	79	75	72	78	75	72	77	74	72	71	71	71	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1026107
5°	831106
10°	538974
15°	373044
20°	260603
25°	156632
30°	16515
35°	1599
40°	959
45°	589
50°	571
55°	822
60°	943
65°	739
70°	609
75°	614
80°	600
85°	629



TEST NUMBER: P179745

CATALOG NUMBER: LDA6A65930D010TE LARH20SP 6LAL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1276.3	30.1
10°-20°	1848.9	43.6
20°-30°	1061.5	25.0
30°-40°	31.1	0.7
40°-50°	6.7	0.2
50°-60°	7.3	0.2
60°-70°	6.0	0.1
70°-80°	3.3	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4186.6	98.7
0°-40°	4217.7	99.4
0°-60°	4231.7	99.8
0°-90°	4241.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4241.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18718	
5°	15103	###
15°	6573	1849
25°	2590	1061
35°	24	31
45°	8	7
55°	9	7
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P179745

CATALOG NUMBER: LDA6A65930D010TE LARH20SP 6LAL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	18717.7
2.5°	17695.3
5°	15102.9
7.5°	12470.5
10°	9682.3
12.5°	7902.1
15°	6573.0
17.5°	5559.2
20°	4467.1
22.5°	3502.0
25°	2589.5
27.5°	1225.9
30°	260.9
32.5°	32.5
35°	23.9
37.5°	17.2
40°	13.4
42.5°	10.5
45°	7.6
47.5°	6.7
50°	6.7
52.5°	7.6
55°	8.6
57.5°	8.6
60°	8.6
62.5°	7.6
65°	5.7
67.5°	4.8
70°	3.8
72.5°	3.8
75°	2.9
77.5°	2.9
80°	1.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)