

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179777

Luminaire Tested: **LDA6A65930D010TE LARH40FL 6LAL1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26680)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65930D010TE LARH40FL 6LAL1LI
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4921.2 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 78
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179777

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LAL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179777

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LAL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	96
2	110	107	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	92
3	106	101	97	94	105	100	96	94	98	95	92	95	93	91	93	91	89	88	88	88	88
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	84	84	84
5	99	93	88	85	98	92	87	84	90	86	84	88	85	83	87	84	82	81	81	81	81
6	96	89	84	81	94	88	84	80	87	83	80	85	82	79	84	81	79	78	78	78	78
7	92	85	80	77	91	85	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75
8	89	82	77	74	88	81	77	74	80	76	74	79	76	73	79	75	73	72	72	72	72
9	86	79	74	71	85	78	74	71	78	74	71	77	73	71	76	73	70	69	69	69	69
10	83	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	67	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	791121
5°	617679
10°	541684
15°	495060
20°	361611
25°	176454
30°	43064
35°	9851
40°	2118
45°	961
50°	486
55°	726
60°	735
65°	623
70°	465
75°	402
80°	316
85°	0



TEST NUMBER: P179777

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LAL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1039.9	21.1
10°-20°	2342.5	47.6
20°-30°	1379.9	28.0
30°-40°	134.7	2.7
40°-50°	10.7	0.2
50°-60°	6.1	0.1
60°-70°	4.7	0.1
70°-80°	2.3	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4762.3	96.8
0°-40°	4896.9	99.5
0°-60°	4913.8	99.8
0°-90°	4921.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4921.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14431	
5°	11224	###
15°	8723	2342
25°	2917	1380
35°	147	135
45°	12	11
55°	8	6
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P179777

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LAL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14431.2
2.5°	12916.7
5°	11224.5
7.5°	10379.8
10°	9731.0
12.5°	9259.0
15°	8722.9
17.5°	7779.8
20°	6198.5
22.5°	4470.9
25°	2917.2
27.5°	1741.0
30°	680.3
32.5°	356.4
35°	147.2
37.5°	48.7
40°	29.6
42.5°	19.1
45°	12.4
47.5°	7.6
50°	5.7
52.5°	6.7
55°	7.6
57.5°	6.7
60°	6.7
62.5°	5.7
65°	4.8
67.5°	3.8
70°	2.9
72.5°	2.9
75°	1.9
77.5°	1.9
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)