

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179825

Luminaire Tested: **LDA6A65930D010TE LARH40FL 6LFC1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P179825  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26683)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA6A65930D010TE LARH40FL 6LFC1H  
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 40° Flood  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5395.2 lumens  
Efficiency: N/A  
Efficacy: 69.2 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.61  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 78  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P179825

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LFC1H

### Luminous Intensity Polar Plot





TEST NUMBER: P179825

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LFC1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96			
2	110	107	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88			
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			
5	99	93	88	85	98	92	88	84	90	86	84	89	85	83	87	84	82	81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			
7	92	85	81	77	91	85	80	77	83	80	77	82	79	76	81	78	76	75			
8	89	82	77	74	88	81	77	74	80	77	74	80	76	73	79	76	73	72			
9	86	79	74	71	85	78	74	71	78	74	71	77	73	71	76	73	70	69			
10	84	76	72	69	83	76	71	68	75	71	68	74	71	68	74	70	68	67			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	736290
5°	664796
10°	604977
15°	553028
20°	403614
25°	198780
30°	43070
35°	8185
40°	2190
45°	961
50°	571
55°	459
60°	417
65°	376
70°	305
75°	212
80°	0
85°	0



TEST NUMBER: P179825

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LFC1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1117.4	20.7
10°-20°	2617.6	48.5
20°-30°	1510.0	28.0
30°-40°	131.3	2.4
40°-50°	10.9	0.2
50°-60°	4.4	0.1
60°-70°	2.6	0.0
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5244.9	97.2
0°-40°	5376.2	99.6
0°-60°	5391.5	99.9
0°-90°	5395.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5395.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13431	
5°	12081	###
15°	9744	2618
25°	3286	1510
35°	122	131
45°	12	11
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179825

CATALOG NUMBER: LDA6A65930D010TE LARH40FL 6LFC1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13431.0
2.5°	12757.3
5°	12080.7
7.5°	11448.1
10°	10868.0
12.5°	10368.3
15°	9744.3
17.5°	8686.4
20°	6918.5
22.5°	5008.3
25°	3286.3
27.5°	1702.9
30°	680.4
32.5°	357.4
35°	122.3
37.5°	50.6
40°	30.6
42.5°	19.1
45°	12.4
47.5°	7.6
50°	6.7
52.5°	5.7
55°	4.8
57.5°	3.8
60°	3.8
62.5°	2.9
65°	2.9
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)