

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204387

Luminaire Tested: **LSR6B30D010BZ EC6B30509027 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509027 6LBSGPH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2319.3 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204387

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204387

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76																			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66																			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57																			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50																			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45																			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32																			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204387

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.4	4.4
10°-20°	284.7	12.3
20°-30°	415.2	17.9
30°-40°	473.5	20.4
40°-50°	454.2	19.6
50°-60°	347.9	15.0
60°-70°	190.9	8.2
70°-80°	50.8	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.3	34.5
0°-40°	1274.8	55.0
0°-60°	2076.9	89.5
0°-90°	2319.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2319.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1077	
5°	1069	101
15°	1010	285
25°	902	415
35°	757	473
45°	590	454
55°	390	348
65°	192	191
75°	44	51
85°	0	1
90°	0	



TEST NUMBER: P204387

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1077.2
2.5°	1074.4
5°	1068.8
7.5°	1060.5
10°	1049.3
12.5°	1029.9
15°	1010.4
17.5°	988.1
20°	963.0
22.5°	932.4
25°	901.8
27.5°	871.2
30°	832.2
32.5°	796.0
35°	757.1
37.5°	718.1
40°	679.1
42.5°	637.4
45°	590.1
47.5°	542.8
50°	492.7
52.5°	439.8
55°	389.7
57.5°	339.6
60°	286.7
62.5°	236.6
65°	192.1
67.5°	147.5
70°	108.6
72.5°	72.4
75°	44.5
77.5°	19.5
80°	5.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)