

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203048

Luminaire Tested: **LSR6B30D010BZ EC6B30509027 6LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509027 6LBWB1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1365.4 lumens  
Efficiency: N/A  
Efficacy: 48.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203048

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203048

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |     |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |     |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98  | 97  | 96  | 95  | 94  | 92  |    |    | 92  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  | 93  | 90  | 88  | 90  | 88  | 86  | 84  |    |    | 84  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 100 | 93  | 87  | 83  | 98  | 92  | 86  | 82  | 89  | 85  | 81  | 86  | 83  | 80  | 84  | 81  | 78  | 77  |    |    | 77  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 78  | 75  | 72  | 70  |    |    | 70  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 66  | 64  |    |    | 64  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 83  | 73  | 67  | 62  | 82  | 72  | 66  | 61  | 71  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 60  | 59  |    |    | 59  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  | 65  | 60  | 56  | 63  | 59  | 55  | 54  |    |    | 54  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 74  | 63  | 57  | 52  | 73  | 63  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 51  | 59  | 55  | 51  | 50  |    |    | 50  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 70  | 59  | 52  | 48  | 69  | 58  | 52  | 48  | 57  | 52  | 48  | 57  | 51  | 47  | 56  | 51  | 47  | 46  |    |    | 46  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 66  | 55  | 49  | 44  | 65  | 55  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 44  | 52  | 47  | 44  | 42  |    |    | 42  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203048

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBWB1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 96.8   | 7.1       |
| 10°-20°   | 270.6  | 19.8      |
| 20°-30°   | 379.0  | 27.8      |
| 30°-40°   | 361.9  | 26.5      |
| 40°-50°   | 206.1  | 15.1      |
| 50°-60°   | 50.3   | 3.7       |
| 60°-70°   | 0.7    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 746.3  | 54.7      |
| 0°-40°    | 1108.3 | 81.2      |
| 0°-60°    | 1364.7 | 100.0     |
| 0°-90°    | 1365.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1365.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1029 |      |
| 5°  | 1021 | 97   |
| 15° | 960  | 271  |
| 25° | 829  | 379  |
| 35° | 590  | 362  |
| 45° | 264  | 206  |
| 55° | 50   | 50   |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P203048

CATALOG NUMBER: LSR6B30D010BZ EC6B30509027 6LBWB1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1029.1 |
| 2.5°  | 1029.1 |
| 5°    | 1020.7 |
| 7.5°  | 1009.6 |
| 10°   | 1001.2 |
| 12.5° | 984.6  |
| 15°   | 959.5  |
| 17.5° | 937.3  |
| 20°   | 909.5  |
| 22.5° | 873.3  |
| 25°   | 828.8  |
| 27.5° | 778.7  |
| 30°   | 723.1  |
| 32.5° | 656.4  |
| 35°   | 589.6  |
| 37.5° | 509.0  |
| 40°   | 422.7  |
| 42.5° | 342.1  |
| 45°   | 264.2  |
| 47.5° | 194.7  |
| 50°   | 136.3  |
| 52.5° | 86.2   |
| 55°   | 50.1   |
| 57.5° | 22.2   |
| 60°   | 5.6    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)