

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179759

Luminaire Tested: **LDA6A65840D010TE LARH30NF 6LAL1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P179759  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26679)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA6A65840D010TE LARH30NF 6LAL1LI  
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6045.2 lumens  
Efficiency: N/A  
Efficacy: 77.5 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.51  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 78  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P179759

CATALOG NUMBER: LDA6A65840D010TE LARH30NF 6LAL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P179759

CATALOG NUMBER: LDA6A65840D010TE LARH30NF 6LAL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86			
5	100	94	89	86	99	93	89	86	91	88	85	90	87	84	88	86	84	82			
6	97	90	86	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80			
7	94	87	82	79	93	86	82	79	85	81	79	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	71	76	73	70	69			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1127289
5°	924915
10°	802885
15°	608131
20°	361418
25°	196886
30°	50850
35°	4752
40°	2018
45°	1047
50°	520
55°	822
60°	800
65°	636
70°	593
75°	508
80°	379
85°	0



TEST NUMBER: P179759

CATALOG NUMBER: LDA6A65840D010TE LARH30NF 6LAL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1546.6	25.6
10°-20°	2869.8	47.5
20°-30°	1472.7	24.4
30°-40°	129.4	2.1
40°-50°	11.4	0.2
50°-60°	7.0	0.1
60°-70°	5.0	0.1
70°-80°	2.9	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5889.1	97.4
0°-40°	6018.4	99.6
0°-60°	6036.9	99.9
0°-90°	6045.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6045.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	20563	
5°	16808	###
15°	10715	2870
25°	3255	1473
35°	71	129
45°	14	11
55°	9	7
65°	5	5
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P179759

CATALOG NUMBER: LDA6A65840D010TE LARH30NF 6LAL1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	20563.4
2.5°	18872.2
5°	16807.6
7.5°	15579.3
10°	14423.3
12.5°	12950.1
15°	10715.2
17.5°	8285.6
20°	6195.2
22.5°	4524.9
25°	3255.0
27.5°	2057.3
30°	803.3
32.5°	352.7
35°	71.0
37.5°	40.4
40°	28.2
42.5°	19.6
45°	13.5
47.5°	9.8
50°	6.1
52.5°	7.3
55°	8.6
57.5°	8.6
60°	7.3
62.5°	6.1
65°	4.9
67.5°	3.7
70°	3.7
72.5°	3.7
75°	2.4
77.5°	2.4
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)