

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P252757

Luminaire Tested: **LE_6B10D010 EC6B10209024 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209024 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1221.3 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252757

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252757

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56			
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51			
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54646
5°	54147
10°	52958
15°	51271
20°	49196
25°	46186
30°	39964
35°	31125
40°	23659
45°	18444
50°	15285
55°	13717
60°	12500
65°	11547
70°	10587
75°	9831
80°	8867
85°	8159



TEST NUMBER: P252757

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	6.4
10°-20°	213.3	17.5
20°-30°	290.5	23.8
30°-40°	245.8	20.1
40°-50°	157.7	12.9
50°-60°	108.5	8.9
60°-70°	74.2	6.1
70°-80°	41.2	3.4
80°-90°	12.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.8	47.6
0°-40°	827.6	67.8
0°-60°	1093.8	89.6
0°-90°	1221.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1221.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	838	
5°	827	78
15°	759	213
25°	642	290
35°	391	246
45°	200	158
55°	121	108
65°	75	74
75°	39	41
85°	11	12
90°	0	



TEST NUMBER: P252757

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	837.6
2.5°	834.5
5°	826.8
7.5°	814.6
10°	799.4
12.5°	780.1
15°	759.1
17.5°	734.9
20°	708.6
22.5°	679.2
25°	641.6
27.5°	590.5
30°	530.5
32.5°	461.6
35°	390.8
37.5°	328.8
40°	277.8
42.5°	235.0
45°	199.9
47.5°	172.4
50°	150.6
52.5°	134.1
55°	120.6
57.5°	107.9
60°	95.8
62.5°	84.9
65°	74.8
67.5°	64.5
70°	55.5
72.5°	46.6
75°	39.0
77.5°	31.2
80°	23.6
82.5°	17.2
85°	10.9
87.5°	4.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)