

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203112

Luminaire Tested: **LE\_6B10D010 EC6B10209024 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203112  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209024 6LBWMW1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 907.1 lumens  
Efficiency: N/A  
Efficacy: 91.6 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203112

CATALOG NUMBER: LE\_6B10D010 EC6B10209024 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203112

CATALOG NUMBER: LE\_6B10D010 EC6B10209024 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203112

CATALOG NUMBER: LE\_6B10D010 EC6B10209024 6LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.0	5.3
10°-20°	134.5	14.8
20°-30°	193.9	21.4
30°-40°	201.3	22.2
40°-50°	148.8	16.4
50°-60°	88.9	9.8
60°-70°	54.0	6.0
70°-80°	29.6	3.3
80°-90°	8.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.4	41.5
0°-40°	577.6	63.7
0°-60°	815.3	89.9
0°-90°	907.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	907.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	509	
5°	506	48
15°	478	135
25°	422	194
35°	325	201
45°	192	149
55°	97	89
65°	54	54
75°	28	30
85°	7	8
90°	0	



TEST NUMBER: P203112

CATALOG NUMBER: LE\_6B10D010 EC6B10209024 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	509.4
2.5°	509.4
5°	506.1
7.5°	501.8
10°	495.1
12.5°	487.4
15°	477.5
17.5°	466.5
20°	455.5
22.5°	440.1
25°	422.5
27.5°	403.8
30°	379.6
32.5°	355.4
35°	324.6
37.5°	292.6
40°	257.5
42.5°	223.4
45°	191.5
47.5°	162.9
50°	137.5
52.5°	115.5
55°	96.9
57.5°	82.5
60°	70.4
62.5°	61.6
65°	53.9
67.5°	47.2
70°	40.8
72.5°	34.1
75°	27.5
77.5°	22.0
80°	16.5
82.5°	12.1
85°	6.6
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)